


## **TOP VIEW**



## SIDE VIEW



## **BOTTOM VIEW**



Specifications			Notes		Revision History					
Description	Value	Unit	Notes		Version	Description		Date	Approved	
Technology	Electro-Mechanical		1) All dimensions are in mm unless otherwise noted		1	Released from Engineering			10/21/2013	J.S
Resonant Frequency	2,300	(Hz)	2) All parts meet RoHS							
Rated Voltage	5	(V)								
SPL @ 10cm	85	(dBA)								
Tone	Single									
Mount Type	Thru Hole									
Voltage Range	4~7	(V)								
Max Rated Current	30	(mA)								
Housing Material	NORYL				Drawn by	Date	Checked by	Date	Approved by	Date
Operating Temperature	-30 ~ +70	°C			A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
Storage Temperature	-40 ~ +85	°C		Flortro Machanical Ind	icator	tor   IE122305-7				
Weight	2	(g)		Electro-Mechanical Indicator		IET57202-1				

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.