



| | Part Number: | t Number: | | 0.10.10004 | |
|--------|--------------|-----------|----------|------------|--|
| | בחבחד | 012.1 | CJ | 8/9/2021 | |
| IP3030 | | 012-1 | CHECKED | 8/10/2021 | |
| | | | L.L. | 0/10/2021 | |
| | Description: | | APPROVED | 0/40/2024 | |
| | Piezo I | Indicator | J.S. | 8/10/2021 | |

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View



Side View



Bottom View



Additional considerations can be found at www.dbunlimitedco.com/technical-articles.

| Items | Specifications | Conditions | | | | | | |
|---------------------------|----------------|-------------|-----|---|------------|----------|--|--|
| Min. Sound Pressure Level | 100 | dB (@ 10cm) | | | | | | |
| Tone | Single | | | | | | | |
| Resonant Frequency | 3,000 | Hz | | | | | | |
| Rated Voltage | 12 | V | | REVISION HISTORY | | | | |
| Voltage Range | 3 ~ 20 | V | REV | DESCRIPTION | DATE | APPROVED | | |
| Max. Rated Current | 10 | mA | | Released from Engineering | 10/21/2013 | J.S. | | |
| Storage Temperature | -30 ~ +70 | °C | 1 | Updated drawing, temperature and weight | 8/10/2021 | L.L. | | |
| Operating Temperature | -20 ~ +60 | °C | | NOTES | | | | |
| Connection Method | PC Pin | | | All dimensions are in mm unless otherwise noted | | | | |
| Mount Type | Thru Hole | | | 2) All tolerances are ± 0.5 mm unless otherwise noted | | | | |
| Housing Material | ABS | | | 3) All parts meet RoHS | | | | |
| Weight | 7 | g | | 4) Subject to change or redrawn without notice | | | | |