



			1	
	Part Number:		DRAWN	0/7/2047
	TE122	2403-1	CJ	9/7/2017
			CHECKED	9/7/2017
			P.D.	
	Description:	anical Indicator	APPROVED	9/7/2017
	LIECTIO-MECH		C.E.	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View



Side View



Bottom View



	Items	Specifications	Conditions				
Γ	Min. Sound Pressure Level	75	dB (@ 10cm)				
A	Tone	Single		REVISION HISTORY			
	Resonant Frequency	2,400 ± 400	Hz	REV	DESCRIPTION	DATE	APPROVED
	Rated Voltage	3	V		Released from Engineering	10/21/2013	J.S.
	Voltage Range	2 ~ 5	V		Updated template, corrected height, added polarity	10/21/2013	J.3.
	Max. Rated Current	30	mA	1	markings	9/7/2017	C.E.
	Storage Temperature	-40 ~ +85	°C	NOTES			
	Operating Temperature	-30 ~ +70	°C	All dimensions are in mm unless otherwise noted			
	Connection Method	Surface Mount Pads		2) All tolerances are ± 0.5 mm unless otherwise noted			
	Mount Type	Surface Mount		3) All parts meet RoHS			
	Housing Material	PPS		4) Subject to change or redrawn without notice			
	*** * * * *	_					