

TOP VIEW



SIDE VIEW



Specifications			Notes		Revision History					
Description	Value	Unit	Notes		Version	Description			Date	Approved
Resonant Frequency	3,500	(Hz)	1) All dimensions are in mm unless otherwise noted		1	Released from Engineering			10/21/2013	J.S
Resonant Impedance (Max)	2,500	(Ohm)	2) All parts meet RoHS							
Max Input Voltage	20	(V)								
Capacitance	12,000	(pF)								
Plate Material	Stainless Steel									
Operating Temperature	-20 ~ +60	°C								
Storage Temperature	-20 ~ +70	°C								
		+			Drawn by	Date	Checked by	Date	Approved by	Date
					A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
			DB UNLIMITED	Piezo Bender		P27035-1				

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.