


			1		
	Part Number:		DRAWN		
	TE102603-1		CJ	12/9/2016	
	I ETUZ	2003-1	CHECKED	12/9/2016	
			P.D.		
	Description:	anical Transducer	APPROVED	12/9/2016	
	Electro-Mecha		J.S.		

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View




0.38

Weight

Side View



Bottom View



4) Subject to change or redrawn without notice

Items	Specifications	Conditions						
Sound Pressure Level	88	dB (@ 10cm)						
Resonant Frequency	2,670	Hz						
Rated Voltage	3.6	V		REVISION HISTORY				
Voltage Range	2.5 ~ 4.5	V	REV	DESCRIPTION	DATE	APPROVED		
Coil Resistance	16	Ω		Released from Engineering	10/21/2013	J.S.		
Max. Rated Current	100	mA	1	Updated to new template	12/9/2016	J.S.		
Storage Temperature	-40 ~ +85	°C	2	Updated storage temp, voltage range	5/20/2019	C.E.		
Operating Temperature	-30 ~ +70	℃		NOTES				
Connection Method	Surface Pads			All dimensions are in mm unless otherwise noted				
Mount Type	Surface Mount			2) All tolerances are ± 0.5 mm unless otherwise noted				
Housing Material	LCP			3) All parts meet RoHS				