

Sp	pecifications		Notes Version 1) All dimensions are in mm unless otherwise noted 1			Revision History				
Description	Value	Unit			Version	Description			Date	Approved
Resonant Frequency	4,300	(Hz)			1	Released from Engineering		10/21/2013	J.S	
Resonant Impedance (Max)	300	(Ohm)	2) All parts meet RoHS							
Max Input Voltage	30	(V)								
Capacitance	25,000	(pF)								
Plate Material	Alloy									
Operating Temperature	-20 ~ +60	°C								
Storage Temperature	-20 ~ +70	°C								
			 (Drawn by	Date	Checked by	Date	Approved by	Date
					A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
			DB UNLIMITED	Piezo Bender		P15043-1				

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.