



			1		
	Part Number:	060-1	DRAWN	10/21/2012	
	D1 F		CJ	10/21/2013	
	P150		CHECKED	10/21/2013	
			C.E.	10, 11, 1010	
	Description: Piezo	Bender	APPROVED	10/21/2013	
			J.S.	10,21,2015	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com

Top View



Side View



				REVISION HISTORY			
Items	Specifications	Conditions	REV	DESCRIPTION	DATE	APPROVED	
Resonant Frequency	6,000	Hz		Released from Engineering	10/21/2013	J.S.	
Max Input Voltage	30	Vp-p	1	Updated template, ceramic dimension	12/22/2023	P.D.	
Resonant Impedance (Max)	300	Ω		NOTES			
Capacitance	15,000	pF		1) All dimensions are in mm unless otherwise noted			
Storage Temperature	-20 ~ +70	°C		2) All tolerances are ± 0.5 mm unless otherwise noted			

°C

-20 ~ +60

Brass

Operating Temperature

Plate Material

3) All parts meet RoHS

4) Subject to change or redrawn without notice