

Spe	cifications		- Notes		Revision History					
Description	Value	Unit			Version		Description		Date	Approved
Resonant Frequency	3,600	(Hz)	1) All dimensions are in mm	1	Released from Engineering			10/21/2013	J.S	
Resonant Impedance (Max)	600	(Ohm)	2) All parts meet RoHS							
Max Input Voltage	30	(V)								
Capacitance	27,000	(pF)								
Plate Material	Brass									
Operating Temperature	-20 ~ +60	°C								
Storage Temperature	-20 ~ +70	°C								
	+				Drawn by	Date	Checked by	Date	Approved by	Date
					A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013
			DB UNLIMITED	Piezo Bender		P20036-2			5-2	

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.