

Features

- Can be used without external DC bias
- Exhibits uniform R_v characteristics
- High Voltage Sensitivity
- P Type Schottky Diode
- Available in chip form (ODS-1261)
- RoHS Compliant* and 260°C Reflow Compatible

Description and Applications

The MA4E931Z2-1261A Zero Bias Detector (ZBD) diode is suitable for use in microstrip or stripline detector circuits. These chips can be used in automatic assembly processes due to their 0.004" gold bond pads and sturdy construction. Designed for high volume, low cost, detector applications.

Maximum Ratings


Parameter	Symbol	Unit	Values
Operating Temperature	T_{OP}	°C	-65 to +150
Storage Temperature	T_{STG}	°C	-65 to +150
Incident RF Power (CW)	P_T	mW	75
Reverse Voltage @ 25 °C	V_R	V	3

Electrical Specifications @ +25 °C

Parameter	Condition	Symbo	Specificatio
Breakdown Voltage	$I_R = 1.0$ mA	V_B	3.0 V min.
Forward Voltage	$I_F = 1.0$ mA	V_F	150 mV typ.

Chip Outline

MA4E931Z2-1261A



RF Performance @ 10.0 GHz @ +25 °C

Parameter	Conditions	Typical
Tangential Signal Sensitivity	BW = 2 MHz Video NF = 3.5 dB	-52 dBm min
Video Impedance (R_v)	BW = 2 MHz	2.5K Ω min 4.5K Ω max
Voltage Output (E_o)	BW = 2 MHz	5.0 mV min

* Restrictions on Hazardous Substances, European Union Directive 2002/95/EC.

M/A-COM Technology Solutions Inc. All rights reserved.

Information in this document is provided in connection with M/A-COM Technology Solutions Inc ("MACOM") products. These materials are provided by MACOM as a service to its customers and may be used for informational purposes only. Except as provided in MACOM's Terms and Conditions of Sale for such products or in any separate agreement related to this document, MACOM assumes no liability whatsoever. MACOM assumes no responsibility for errors or omissions in these materials. MACOM may make changes to specifications and product descriptions at any time, without notice. MACOM makes no commitment to update the information and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to its specifications and product descriptions. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document.

THESE MATERIALS ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, CONSEQUENTIAL OR INCIDENTAL DAMAGES, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT. MACOM FURTHER DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. MACOM SHALL NOT BE LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS, WHICH MAY RESULT FROM THE USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.

2

M/A-COM Technology Solutions Inc. (MACOM) and its affiliates reserve the right to make changes to the product(s) or information contained herein without notice.
Visit www.macom.com for additional data sheets and product information.