

# Product data sheet

## Characteristics

# 9007AW12M16

Limit switch, 9007, 600 VAC 15amp aw  
+options



### Main

Body type	Standard
Device short name	AW
Series name	Heavy duty

### Complementary

Line Rated Current	15 A
Body material	Cast zinc
Contact operation	Snap action
Fluid connection type	0.5 inch BSP conduit entrance
Maximum displacement angle	30 °
Switch actuation	CCW
Tilting angle	5 °
Torque Value	2.75 lbf.in (0.31 N.m)
Tripping angle	2.5 °

### Environment

Ambient Air Temperature for Operation	-60...185 °F (-51...85 °C)
NEMA Degree of Protection	NEMA 1/2/4/12/13
Product Certifications	CSA LR25490 class 3211 03[RETURN]CE[RETURN]JUL listed file E42259 CCN NKCR

### Ordering and shipping details

Category	US10DS121496
Discount Schedule	0DS1
GTIN	785901607632
Returnability	No
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	1.70 in (4.318 cm)
Package 1 Width	2.80 in (7.112 cm)
Package 1 Length	5.20 in (13.208 cm)
Package 1 Weight	20.00 oz (566.991 g)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------