



### Main

Device short name	C
Head type	Wobble stick
Series name	Heavy duty

### Complementary

Line Rated Current	10 A
Body material	Zinc alloy
Contacts material	Gold flashed contacts
Contact operation	Snap action
Maximum displacement angle	90 °
Switch actuation	Any direction
Tilting angle	10 °
Torque Value	3 lbf.in (0.34 N.m)
Tripping angle	3 °
Type of operator	Wire extension

### Environment

Ambient Air Temperature for Operation	0...185 °F (-18...85 °C)
Product Certifications	UL Listed[RETURN]CSA[RETURN]CE

### Ordering and shipping details

Category	US10DS121499
Discount Schedule	0DS1
GTIN	785901231103
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.54 in (6.452 cm)
Package 1 Width	1.00 in (2.54 cm)
Package 1 Length	6.45 in (16.387 cm)
Package 1 Weight	21.76 oz (616.886 g)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------