MALLORY Mallory Sonalert Products Inc. Part # PK-26N04W-12VQ Sales Outline Drawing B

May not be suitable for all medical and aerospace applications. Specifications: Contact Mallory Sonalert to discuss your application.

Resonant Frequency (Hz) 400 ± 100 Operating Voltage (Vdc) $8 \sim 16$ Rated Voltage (Vdc) 12

Current Consumption Max. (mA) 40 at Rated Voltage Sound Pressure Level Min. (dB) 87 at 30cm at Rated Voltage

Tone/Pulse Rate Constant
Operating Temperature (°C) $-20 \sim +70$ Storage Temperature (°C) $-30 \sim +80$

Housing ABS 757 plastic resin (Color: Black)
Lead Wire 24 AWG
Weight (Grams) 14

Options For other options contact factory

Dimensions: (units: mm) **ROHS Compliant**



