MALLORY Mallory Sonalert Products Inc. Sales Outline Drawing		Part #	PL-21N30WQ	
		Revision	С	
May not be suitable for	all medical a	nd aero	space application	
Specifications: Contact Mallory Sonale	rt to discuss	your ap	plication.	
Oscillation Frequency (Hz)	3000 ± 500			
Operating Voltage (Vdc)	3 ~ 30			
Rated Voltage (Vdc)	12			
Current Consumption (mA/max)	12 at Rated Voltage			
Sound Pressure Level (dB/min)	80 at 30cm at Rated voltage			
Tone/Pulse Rate (Hz)	Slow Pulse 1.2 $\pm 20\%$			
Operating Temperature (°C)	-20 ~ +70			
Storage Temperature (°C)	-30 ~ +80			
C C			plastic resin	
	(Color: Black)			
Lead Wires	28 AWG			
Weight (Grams)	3.2			
Condition by wave soldering (°C)	$245 \pm 5 / 3 \pm 0.5 \text{ sec}$			
Condition by hand soldering (°C)	350 ± 20 / within 5 sec			
Options	For other of	other options contact factory		
		R	oHS Compliant	

Dimensions: (units: mm)

