



Main

Device short name	L300
Series name	Severe duty

Complementary

Line Rated Current	20 A
AWG gauge	AWG 12 1 AWG 14 2
Body material	Cast aluminium
Contact code designation	A600 P600
Contact operation	Double-break isolated
Contacts material	Silver alloy (Ag/Ni)
Contact operation	Slow make slow break
Function Available	Neutral position
Material	Metal: front cover
Mounting support	panel
Switch Function	2-pole switch
Torque Value	95 ozf.in
Connector type	4 pins male

Environment

Ambient Air Temperature for Operation	0...200 °F (-18...93 °C)
NEMA Degree of Protection	NEMA 1/4/13
Product Certifications	UL listed file E42259 CCN NKCR[RETURN]CSA LR25490 class 3211 03[RETURN]CE
Vibration resistance	30 gn 10...55 Hz)

Ordering and shipping details

Category	US10DS122426
Discount Schedule	ODS1
GTIN	785901171850
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.54 in (6.452 cm)
Package 1 Width	1.00 in (2.54 cm)
Package 1 Length	6.45 in (16.387 cm)
Package 1 Weight	24.00 oz (680.389 g)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------