



Main

Range	Square D X Series
Product or Component Type	Switch
Device Application	Control
Device presentation	Mechanism with fixing frame
Aesthetic name	X Series

Complementary

Actuator	Rocker
Number of gangs	1 gang
Switch Function	3-way
Number of poles	1
Local signalling	1 LED
Signalling function	Status
Signalling colour	Blue
[Ie] rated operational current AC	15 A
[Ue] rated operational voltage	120 V
Network type	AC
Network Frequency	60 Hz
Communication Network Type	Wi-Fi
Mounting Mode	By screws
Device mounting	Flush
Material	Plastic strap Metal fixing frame
Color	Light almond
Surface Finish	Matte
Connections - terminals	Phase and neutral 4 screw terminal AWG 14...AWG 12) copper Earth 1 screw terminal copper
Width	1.73 in (44 mm)
Height	4.09 in (104 mm)
Depth	1.77 in (45 mm)
Quantity per Set	1 piece

Ordering and shipping details

Category	09930-WD CONNECTED DEVICES
Discount Schedule	DE9
GTIN	3606482012554
Nbr. of units in pkg.	1
Package weight(Lbs)	5.26 oz (149.0 g)
Returnability	Yes
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.17 in (10.6 cm)
Package 1 width	2.13 in (5.4 cm)
Package 1 Length	2.17 in (5.5 cm)
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Weight	3.51 lb(US) (1.594 kg)
Package 2 Height	4.45 in (11.3 cm)
Package 2 width	4.61 in (11.7 cm)
Package 2 Length	11.02 in (28 cm)
Unit Type of Package 3	PAL
Number of Units in Package 3	1920
Package 3 Weight	813.62 lb(US) (369.05 kg)
Package 3 Height	47.24 in (120 cm)
Package 3 width	39.37 in (100 cm)
Package 3 Length	47.24 in (120 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	2 years
----------	---------