Part # MALLORY v Sonalert Products Inc. **ASI401TRQ** Revision **Sales Outline Drawing**

May not be suitable for all medical and aerospace applications.

Specifications: Contact Mallory Sonalert to discuss your application.

Oscillation Frequency (Hz) 2400 + 300Operating Voltage (Vdc) $9.0 \sim 15$ Rated Voltage (Vdc) 12

Current Consumption Max. (mA) 50 at Rated Voltage 90 at 10cm at Rated Voltage Sound Pressure Level Min. (dB)

Tone/Pulse Rate

Operating Temperature (°C) Storage Temperature (°C)

Housing

Type of Connection

Weight (Grams)

Condition by reflow soldering (°C)

Condition by hand soldering (°C)

Options

Constant

 $-40 \sim +80$

 $-40 \sim +80$


PPS plastic resin (Color: Gray)

SMD

3.0 250 ± 5 / within 5 sec

 350 ± 20 / within 5 sec

For other options contact factory



Packaging:

Parts are supplied on reels (250 pcs per tape and reel).

Parts come with wash label and are suitable for aqueous wash.