| MALLORY Mallory Sonalert Products Inc. | Part # | PFD-20A35EWQ |
|--|----------|--------------|
| Sales Outline Drawing | Revision | E |

May not be suitable for all medical and aerospace applications. Specifications: Contact Mallory Sonalert to discuss your application.

| Oscillation Frequency (Hz) | 3500 ± 500 |
|----------------------------|----------------|
| Operating Voltage (Vdc) | 3 ~ 24 |
| Rated Voltage (Vdc) | 12 |

Operating Temperature (°C)
$$-20 \sim +70$$

Storage Temperature (°C) $-30 \sim +80$

RoHS Compliant

Dimensions: (units: mm)

Black to (-) and Red to (+) – Constant
Blue to (-) and Red to (+) - Pulse

