MALLORY Mallory Sonalert Products Inc. Part # PK-27N25PSQ Sales Outline Drawing B

May not be suitable for all medical and aerospace applications. Specifications: Contact Mallory Sonalert to discuss your application.

Resonant Frequency (Hz)	2500 ± 500
Operating Voltage (Vdc)	3 ~ 28
Rated Voltage (Vdc)	12

I one/Pulse Rate	Constant
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80

	(Color. Diack)
Leading Pin	Tin Plated Brass
Weight (Grams)	6.4

Options For other options contact factory

RoHS Compliant

Dimensions: (units: mm)

