MALLORY Mallory Sonalert Products Inc.	Part #	PLD-35A29WQ
Sales Outline Drawing	Revision	C

May not be suitable for all medical and aerospace applications. Specifications: Contact Mallory Sonalert to discuss your application.

Oscillation Frequency (Hz)	2900 ± 500
Operating Voltage (Vdc)	3 ~ 24
Rated Voltage (Vdc)	12
Current Consumption (mA/max)	10 at Rated Voltage
Sound Pressure Level (dB/min)	95 at 30cm at Rated voltage
Tone/Pulse Rate (Hz)	Constant + Slow Pulse 1.2 ±20%
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 757 UL94HB plastic resin
	(Color: Black)
Lead Wire	28 AWG
Weight (Grams)	14.2
Condition by wave soldering (°C)	$245 \pm 5 / 3 \pm 0.5 \text{ sec}$

PS: Vp-p = 1/2duty, square wave

Condition by hand soldering (°C)

For other options contact factory

RoHS Compliant

 350 ± 20 / within 5 sec

Dimensions: (units: mm)

Options

