




Mechanical Dimensions: Inches [mm]



Mounting Hole



Circuit Diagram



Electrical Specifications

Rating	16A 125V AC 1/3HP, 10A 250V AC 1/2HP 16(4)A 125/250V AC R_{A}
Contact Resistance	50m ohm Max.
Insulation Resistance	DC 500V 100m ohm Min
Dielectric Strength	AC 1500V 1 minute
Operation Temperature	-20 °C~ 85°C

Material Specifications

Frame	Black, Nylon 66
Actuator	Black, Nylon 66

Rev **Date of issue** **Revision Notes**

Designed **Approved**

A	12-01-2021	Initial Drawing	RC	OF
---	------------	-----------------	----	----