TOP VIEWSIDE VIEWNUTImage: state of the stat											
Specifica	ations		Revision History								
Description	Value Unit		Notes		Version	Description		Date	Approved		
Technology	Piezo	1	 All dimensions are in mm unless otherwise noted 		1	Released from Engineering			10/21/2013	J.S	
Resonant Frequency	3,200	(Hz)	2) All parts meet RoHS				5				
Rated Voltage	24	(V)	1								
SPL @ 10cm	105	(dBA)]								
Tone	Dual]								
Mount Type	Flange										
Voltage Range	3 ~ 28	(V)									
Max Rated Current	30	(mA)									
Housing Material	ABS				Drawn by	Date	Checked by	Date	Approved by	Date	
Operating Temperature	-40 ~ +85	°C			A.B.	10/21/2013	C.E.	10/21/2013	J.S	10/21/2013	
Storage Temperature	-40 ~ +85	°C		Piezo Indicator	-			00000	л <u>1</u>		
/eight 15 (g) DB UNLIMITED Piezo Indicator						IP293224-1					

Additional considerations can be found at www.dbunlimitedco.com/technical-articles.