MALLORY Mallory Sonalert Products Inc.		Part # PL-27A35EPQ		
Sales Outline Drawing		Revision	ⁿ C	
May not be suitable for all medical and aerospace applications. Specifications: Contact Mallory Sonalert to discuss your application.				
Resonant Frequency (Hz) Operating Voltage (Vdc) Rated Voltage (Vdc) Current Consumption Max. (mA) Sound Pressure Level Min. (dB)	3500 ± 500 $3 \sim 24$ 12 15 at Rated Voltage 95 at 30cm at Rated Voltage			
Operating Temperature (°C) Storage Temperature (°C)		w Pulse 1.2 ±20% -20 ~ +70 -30 ~ +80 7 UL94HB plastic resin (Color: Gray)		
Leading Pin Weight (Grams) Options	Tin P For other opti	lated B 21		
Dimensions: (units: mm)			•	Compliant
Ø36.5±0.5 4 19.5±0.2 0 4 0 0 0 0 0 0 0 0 0 0 0 0 0	8 38 # 0.5	43±0.5	7.5±0.5	