
MALLORY Mallory Sonalert Products, Inc. Part #: SCE028LD2VC4F **Sales Outline Drawing** Revision: Α **Specifications:** Sound Level Category: Loud Medium Soft Slow Pulse Mode of Operation: Slow Pulse Slow Pulse Pulse Rate (PPS): 85 to 95 dB(A) Typ. 75 to 85 dB(A) Typ. 65 to 75 dB(A) Typ. Loudness @ 2 FT: 2000 ± 500 Hz 2000 ± 500 Hz Frequency: 2000 ± 500 Hz TERMINALS: BLUE WIRE | TERMINALS: YELLOW **TERMINALS ONLY** Connection: WIRE TO (-) TO (-) Voltage Rating: 16 to 28 VDC **Current Draw:** 40mA MAX Housing Material: 6/6 Nylon, Color: Black -40° to +85° C Storage Temperature: -40° to +85° C Operating Temperature Panel Mounting: Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole. Knurled Nut: Used to attach part to panel. The max recommended torque is 10 in-lbs. Weight (Typical): 2.1 oz (60g)

Dimensions: Inches (mm) ROHS Compliant

NEMA 3R,4X, & 12:

cUL Recognition:

Options:



Approved with use of ACC03. cUL Recognized

Please contact factory.