



**Mallory Sonalert Products, Inc.**

Part #:

**SCE028XD2DP3B**

**Sales Outline Drawing**

Revision:

**C**

**Specifications:**

|                       |  |
|-----------------------|--|
| Sound Level Category  | Extra Loud   |
| Mode of Operation     | Slow Double Pulse @ 0.5 PPS  |
| Voltage Rating        | 16 to 28 VDC   |
| Frequency             | 2000 ± 500 Hz  |
| Loudness @ 2 FT       | 95 to 105 dB(A) Typ.   |
| Current Draw          | 40mA MAX   |
| Housing Material      | 6/6 Nylon, Color: Black  |
| Storage Temperature   | -40° to +85° C   |
| Operating Temperature | -40° to +85° C   |
| Panel Mounting        | Recommended hole size is 1.25"(31.75mm). Thread front will fit standard 30mm(1.181") hole. |
| Knurled Nut           | Used to attach part to panel. The max recommended torque is 10 in-lbs.                     |
| Weight (Typical)      | 2.1 oz (60g)   |
| NEMA 3R,4X, & 12      | Approved with use of ACC03.  |
| cUL Recognition       | cUL Recognized   |
| Options               | Please contact factory.  |

**Dimensions:** Inches (mm)

**ROHS Compliant**

