



		1		
Part Number:	2009-1	DRAWN	4/21/2017	
TD17		CJ	7/21/2017	
IPI/4		CHECKED	4/21/2017	
		P.D.	4/21/2017	
Description:	ransducer	APPROVED	4/21/2017	
Plezo 11		C.E.	4/21/2017	

This document contains data proprietary to DB Unlimited. Any use or reproduction, in any form, without prior written permission of DB Unlimited is prohibited. All terms and conditions can be found at www.dbunlimitedco.com


Top View



Side View



Bottom View



SCALE 10 : 1

Items	Specifications	Conditions						
Sound Pressure Level	>=78	dB (@ 10cm)						
Resonant Frequency	2,000	Hz						
Rated Voltage	9	Vp-p		REVISION HISTORY				
Voltage Range	1 ~ 25	V	REV	DESCRIPTION	DATE	APPROVED		
Capacitance	25,000	pF		Released from Engineering	10/21/2013	J.S.		
Max. Rated Current	7	mA	1	Update operating temp, new drawing template	4/24/2017	C.E.		
Storage Temperature	-40 ~ +85	°C		NOTES				
Operating Temperature	-40 ~ +85	°C		All dimensions are in mm unless otherwise noted				
Connection Method	PC Pins			2) All tolerances are ± 0.5 mm unless otherwise noted				
Mount Type	Thru Hole			3) All parts meet RoHS				
Housing Material	NORYL			4) Subject to change or redrawn without notice				
Weight	1	g						
4		3	Ť	2 Additional considerati	ons can be found at www.dbunli	1 mitedco.com/technical-a		