MALLORY Mallory Sonalert Products Inc.	Part #	PK-35H29W-24VQ
Sales Outline Drawing	Revision	C

May not be suitable for all medical and aerospace applications. Specifications: Contact Mallory Sonalert to discuss your application.

Oscillation Frequency (Hz)	2900 ± 500
Operating Voltage (Vdc)	18 ~ 28
Rated Voltage (Vdc)	24
Current Consumption (mA/max)	30 at Rated Voltage
Sound Pressure Level (dB/min)	100 at 30cm at Rated voltage
Tone/Pulse Rate (Hz0	Constant
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 777D plastic resin
	(Color: Black)
Lead Wires	28 AWG RED & BLACK
Weight (Grams)	13.2

Dimensions: (units: mm) ROHS Compliant

For other options contact factory

Options

