MALLORY Mallory Sonalert Products Inc.	Part #	PLD-21N30PQ
Sales Outline Drawing	Revision	D

May not be suitable for all medical and aerospace applications. Specifications: Contact Mallory Sonalert to discuss your application.

Alarm Type
Oscillation Frequency (Hz)
Operating Voltage (Vdc)
Rated Voltage (Vdc)
Current Consumption (mA/max)
Sound Pressure Level (dB/min)

Tone/Pulse Rate (Hz)

Operating Temperature (°C)

Storage Temperature (°C)

Housing

Lead Wire

Weight (Grams)

Condition by wave soldering (°C)

Condition by hand soldering $(^{\circ}C)$

Options

Indicator (no external circuitry req'd)

 3000 ± 500

 $3 \sim 30$

12

12 at Rated Voltage

80 at 30cm at Rated voltage

Constant + Slow Pulse 1.2 ±20%

 $-20 \sim +70$

 $-30 \sim +80$

ABS 777D UL94HB plastic resin

(Color: Black)

28 AWG

3.0

 $245 \pm 5 / 3 \pm 0.5 \text{ sec}$

 350 ± 20 / within 5 sec

For other options contact factory

RoHS Compliant

Dimensions: (units: mm)

