


# Kinghelm®

| REV    |             | REVISIONS |     |      |
|--------|-------------|-----------|-----|------|
| NUMBER | DESCRIPTION | DWN       | CHK | DATE |
| A      | DESIGN      |           |     |      |



**NOTES:**

1. ELECTRICAL:
  - 1.1. VOLTAGE RATING:DCV 300V 10MS
  - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
  - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
  - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
  - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES
2. MATERIAL:
  - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

| ITEM NO. | PART NUMBER | DESCRIPTION           | QTY. |
|----------|-------------|-----------------------|------|
| ②        | 接头          | 三代IPEX端子              | 1    |
| ①        | 同轴线         | RG0.81白色线, OD: 0.81mm | AS   |

深圳市金航标电子有限公司

www.kinghelm.com.cn

KH-IPEX3-221-RG0.81-WH80

0755-28190160

ALL DIMENSION ARE IN MM

DRAWN *Jamy* DATE 2020-06-15

ENG.

三代IPEX TO OPEN RG0.81白色转接线

COMPUTER GENERATED IN SOLIDWORKS

MFG.

DO NOT SCALE THIS DRAWING

Q.A.



GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ± 1° ± 0.3 ± 0.25 ± 0.150

SIZE Number

**B**

REV

**A**

CUSTOMER PIN:

SCALE: Free

TYPE

SHEET 1 OF 1