

Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			

70±5mm

J1

J2

同向

②

①

②

NOTES:

1. ELECTRICAL:
 - 1.1. VOLTAGE RATING: 60V AC RMS.
 - 1.2. FREQUENCY RANGE: DC 3GHZ
 - 1.3. VSWR: 1.3 MAX.
 - 1.4. CHARACTERISTIC IMPEDANCE: 50 OHMS
2. MATERIAL SEE TABLE:
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
②	端子	高仿 0.81 一代端子, 镀金	2
①	线材	0.81蓝色同轴线, OD:0.81	AS

深圳市金航标电子有限公司

www.kinghelm.com.cn

型号: KH-IPEX-IPEX-RG0.81-BU70

0755-83044319

ALL DIMENSION ARE IN MM	DRAWN	Jamy	DATE	TITLE 一代端子, 同向, 总长70MM	
	ENG.	Ellis	2018 /06/22		
	MFG.	Alan	2018 /06/22		
	Q.A.	Jeff	2018 /06/22		
COMPUTER GENERATED IN SOLIDWORKS DO NOT SCALE THIS DRAWING	PROJECTION			SIZE Number	REV
GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ±1' ±0.3 ±0.25 ±0.150			B		A
SCALE: Free		TYPE		SHEET1 OF 1	

CUSTOMER P/N:

