

Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			

300±10mm

J1

J2

同向

②

①

②

NOTES:

1. ELECTRICAL:
 - 1.1. VOLTAGE RATING: 60V AC RMS.
 - 1.2. FREQUENCY RANGE: DC 3GHZ
 - 1.3. VSWR: 1.3 MAX.
 - 1.4. CHARACTERISTIC IMPEDANCE: 50 OHMS
2. MATERIAL SEE TABLE:
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
②	端子	高仿 0.81 三代端子, 镀金	2
①	线材	0.81蓝色同轴线, OD:0.81	AS

深圳市金航标电子有限公司

www.kinghelm.com.cn

型号: KH-IPEX3-IPEX3-RG0.81-BU300

0755-83044319

ALL DIMENSION ARE IN MM	DRAWN	Jamy	DATE	TITLE 三代端子, 同向, 总长300MM	
	ENG.	Ellis	2018 /06/22		
COMPUTER GENERATED IN SOLIDWORKS DO NOT SCALE THIS DRAWING	MFG.	Alan	2018 /06/22	SIZE Number B	
	Q.A.	Jeff	2018 /06/22		
PROJECTION 	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ±1' ±0.3 ±0.25 ±0.150			SCALE: Free	TYPE
CUSTOMER P/N:				SHEET1 OF 1	