


Kinghelm®

REV		REVISIONS			
NUMBER	DESCRIPTION	DWN	CHK	DATE	
A	DESIGN				



NOTES:

1. ELECTRICAL:
 - 1.1. VOLTAGE RATING:DCV 300V 10MS
 - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
 - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES
2. MATERIAL:
 - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
②	接头	一代IPEX端子	1
①	同轴线	RG1.13白色线, OD: 1.13mm	AS

深圳市金航标电子有限公司 www.kinghelm.com.cn

KH-IPEX4-221-RG1.13-WH60 0755-28190160

ALL DIMENSION ARE IN MM	DRAWN Jamy	DATE 2020-06-15	一代IPEX TO OPEN RG1.13白色转接线
COMPUTER GENERATED IN SOLIDWORKS	ENG.		
DO NOT SCALE THIS DRAWING	MFG.		
PROJECTION	Q.A.		
CUSTOMER PIN:	GENERAL TOLERANCE FOR ANGLES X.X X.XX X.XXX ± 1° ± 0.3 ± 0.25 ± 0.150		SIZE Number B
			REV A
SCALE: Free			TYPE
SHEET 1 OF 1			