


Kinghelm®

REVISIONS					
REV	NUMBER	DESCRIPTION	DWN	CHK	DATE
A		DESIGN			



NOTES:

1. ELECTRICAL:
 - 1.1. VOLTAGE RATING-DCV 300V 10MS
 - 1.2. CONDUCTANCE RESISTANCE: 3.0 OHM/MAX.
 - 1.3. INSULATION RESISTANCE: 5.0M OHM/MIN.
 - 1.4. THE CABLE SHOULD BE 100% ELECTRICAL TEST
 - 1.5. IT SHOULD BE NO ANY OPEN/SHORT, MISWIRING AND INTERMITTENT FAILURES
2. MATERIAL:
 - 2.1. SEE TABLE
3. ALL COMPONENTS ARE RoHS COMPLIANT.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
②	接头	四代IPEX端子	1
①	同轴线	RG0.81 蓝色线, OD:0.81MM	AS

深圳市金航标电子有限公司

www.kinghelm.com.cn

KH-IPEX4-221-RG0.81-BU200

0755-28190160

ALL DIMENSION ARE IN MM	DRAWN	Jamy	DATE	2020-06-15
	ENG.			
COMPUTER GENERATED IN SOLIDWORKS	MFG.			
	Q.A.			

四代IPEX TO OPEN RG0.81蓝色转接线

PROJECTION	GENERAL TOLERANCE FOR ANGLES	X.X	X.XX	X.XXX
		± 1°	± 0.3	± 0.25 ± 0.150

SIZE	Number	REV	A
SCALE: Free	TYPE	SHEET 1 OF 1	

CUSTOMER PIN: