


\*\* Not all features are shown in this drawing. For more detailed information, please contact your Fair-Rite representative.

**UNCONTROLLED ~CATALOG~ DRAWING**

SIZE	PART NO.	REV.
B	2773021447	~



DIMENSIONS  
BOLD NUMBERS ARE IN MILLIMETERS  
LIGHT NUMBERS ARE IN INCHES

**ELECTRICAL SPECIFICATIONS**

Impedance (Ohms)	
10 MHz	25 MHz
65 Min.	70 Min.

**NOTES**

- 1 - WIRE IS OXYGEN FREE, HIGH CONDUCTIVITY COPPER.
- 2 - WIRE MEETS FAIR-RITE PRODUCTS CORP. SOP# ELC-57, FOR SOLDERABILITY.
- 3 - THIS PART MEETS FAIR-RITE PRODUCTS VISUAL INSPECTION CRITERIA FOR SURFACE MOUNT BEADS.
- 4 - PART MEETS FAIR-RITE PRODUCTS SOP# ELC-27, FOR THERMAL SHOCK RESISTANCE.
- 5 - IMPEDANCE MEASURED ON A E4991A USING A 16092A TEST FIXTURE.
- 6 - PART IS SUPPLIED TAPED AND REELED

FR# 73

<b>FAIR-RITE PRODUCTS CORP.</b>				
TITLE SURFACE MOUNT BEAD				
DRAWN BY D. FOOTE	DATE 4/13/2021	SIZE	PART NO.	REV.
CHKD BY		B	2773021447	~
APPRVD BY		SCALE: NONE	SHEET 1 OF 1	