







SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperature Range: -25°C~+85°C
- 4、Contact Resistance: 30mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltage: 800V AC/minute
- 7、Material: Wafer PA66, Beige  
PIN Brass Tin-plated



REV.	DATE	ECN NO.	变更内容 DESCRIPTION	制图 DRAWN



编号	尺寸 (mm)	
	A	B
2*02AW	2.50	7.50
2*03AW	5.00	10.00
2*04AW	7.50	12.50
2*05AW	10.00	15.00
2*06AW	12.50	17.50
2*07AW	15.00	20.00
2*08AW	17.50	22.50
2*09AW	20.00	25.00
2*10AW	22.50	27.50
2*11AW	25.00	30.00
2*12AW	27.50	32.50
2*20AW	47.50	52.50

GENERAL TOLERANCE		钱岳生		料号		版本	
X.X±0.25	X.±2°	制 图	2021、05、03	PART NO.	HC-XHD2.54-2x7AW	REV.	A
X.XX±0.20		审 核	张 名	品 名	XHD2.5等针	页 次	1/1
X.XXX±0.10		核 准	2021、05、04	客 户 料 号	WAFER DIP TYPE	SHEET	1/1
		APPROVAL	张 名	CITM. NO.			
		单 位	2021、05、05				
		单 位	MM	比 例	1:1		
		单 位	SCALE				

深圳市虹成电子有限公司