



RECOMMENDED P. C. B. LAYOUT
(TOP VIEW)

- Specification:
1. Rating : DC 30V 3A;
 2. Contact resistance: $\leq 50m\Omega$;
After test: $\leq 100m\Omega$
 3. Insulation resistance: $\geq 100M\Omega$ (500VDC) ;
After test: $\geq 50M\Omega$
 4. Withstand voltage: 500VAC ;
 5. Insertion and extraction force: 3N~30N;
 6. life test: 5000cycles ;
 7. Operation temperature range: -20°C~70°C
 8. Preservative temperature range: -40°C~85°C

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED				REVISIONS				
					UP TO 5mm: ±0.1	ANGULAR ±1°	NO	DATE	UNIT : MM	ROHS COMPLIANT	DWN	BY	APPD
					ABOVE 5mm: ±0.2				SCALE: 1:1		CHK'D		
6	DC088B 2#CURVE PIECE	BRASS	1	Ag-PLATED	TITLE: DC JACK								
5	DC088 3#SPRING	PHOSPHOR BRONZE	1	Ag-PLATED	MODEL: DC-088A $\phi 1.3$ -PU								
4	DC088 5#FLAT PIECE	BRASS	1	Ag-PLATED									
3	DC005C SOLID PIN	BRASS	1	Ni-PLATED									
2	DC088A COVER	PA10T	1	BLACK									
1	DC088A CASE	PA10T	1	BLACK									

皓宇
HAOYU
DONGGUANG HAOYU ELECTRONICS CO., LTD
东莞市弘皓电子有限公司

PRO.AGI: REV :A0