




P.C.B LAYOUT



SCHEMATIC

注：接触片分两种
1. 铍铜接触片
2. 磷铜接触弹线



SPECIFICATION

1. Rating: DC 12V 0.3A
2. Travel: 2 mm
3. Function: 1P3T
4. Contact Resistance: $\leq 70m\Omega$ MAX
5. Operating Force: $200\pm 80gf$, $350\pm 100gf$
6. Life test: 10,000 cycles

电话：0769-82310511-867

				TOLERANCE								
				UNLESS SPECIFIED		A1	2018.3.5	增加重点尺寸0.15		PWJ		
				UP TO 5mm: ± 0.1	ANGULAR	A0	2018.1.17	初版				
				ABOVE 5mm: ± 0.2	$\pm 1^\circ$	NO	DATE	REVISIONS		BY	APPD	
4	MK22D10 CONTACT/MK23D38 SPRING	BERYLLIUM/PBS	1	Ag-PLATED/NATURAL	TITLE:MINI SLIDE SWITCH			UNIT : MM	ROHS COMPLIANT	DWN		
3	MK23D38 KNOB	PA46	1	BLACK	MODEL: MK-13D38(A)G2-B-E			SCALE: 6:1	CHK'D			
2	MK23D38 COVER	0.2mm SUS	1	WASHING	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司			APPD				
1	MK13D38(A) CASE	PA6T/9# BRASS STRIP	1	BLACK/Ag PLATED				PRO.AGL:		REV :A1		
NO.	PART NAME	MATERIAL	QTY	FINISHING								