



2.0±0.2 TRAVEL *a
 1.5 *c
 2±0.2 TRAVEL *b
 拨柄在中间档



SPECIFICATION

1. Rating: DC 12V 0.3A
 2. Travel: 2 mm
 3. Function: 2P3T
 4. Contact Resistance: ≤70mΩMAX
 5. Operating Force: 200±80gf
 6. Life test: 10,000 cycles
- KNOB X=1.8, 2.0, 2.5, 3.0, 4.0mm
 PA9T无卤料, 拨柄在中间档, 编带方向一致

电话 : 0769-82320511-867

NO.	PART NAME	MATERIAL	QTY	FINISHING
4	MK23D38 SPRING	PBS	2	NATURAL
3	MS23D18 KNOB	PA9T	1	BLACK/WHITE
2	MS23D18 COVER	0.2mm SUS	1	WASHING
1	MS23D20BE CASE	PA9T/9# BRASS STRIP	1	BLACK/Ag PLATED

TOLERANCE UNLESS SPECIFIED									
UP TO 5mm: ±0.1	ANGULAR ±1°	A0	2020.08.04	初版		GYW			
ABOVE 5mm: ±0.2		NO	DATE	REVISIONS		BY		APPD	
TITLE: MINI SLIDE SWITCH				UNIT : MM	ROHS COMPLIANT	DWN			
MODEL: MS-23D20G2-BE-BR9T T7.5				SCALE: 6:1	COMPLIANT	CHK'D			
HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司					APPD				
					PRO.AGL:			REV :A0	