



SPECIFICATION

1. Rating: DC 6V 0.3A
2. Travel: 2 mm
3. Function: 2P3T
4. Contact Resistance: ≤70mΩ MAX
5. Operating Force: 200±80gf, 350±100gf
6. Life test: 10,000 cycles

△ KNOB G=1.8, 2.0, 3.0, 4.0 5.0 5.5mm
 △ T=6.5, 7.5mm

电话 : 0769-82320511-867

				TOLERANCE UNLESS SPECIFIED		REVISIONS		BY		APPD	
UP TO 5mm: ±0.1		ANGULAR ±1°		A4	2023.10.25	△ 新增G5.5柄高规格		GYW			
ABOVE 5mm: ±0.2				A3	2023.03.07	△ 新增尺寸标注		GYW			
				A2	2023.02.02	△ 新增平面度管控		GYW			
				A1	2017.01.09	△ 新增T6.5规格		GYW			
				NO	DATE						
4	MK22D10A	Phosphor copper	2	NATURAL	TITLE:MINI SLIDE SWITCH		UNIT : MM	ROHS COMPLIANT	DWN		
3	MS23D18 KNOB	PA10T	1	BLACK/WHITE	MODEL: MS-23D20G5-B T6.5		SCALE: 6:1		CHK'D		
2	MS23D18 COVER	SUS	1	WASHING	DONGGUANG HAOYU ELECTRONICS CO., LTD				APPD		
1	MS23D20 CASE	PA10T/ BRASS	1	BLACK/Au/Ag PLATED	皓宇 HOOYA 东莞市弘皓电子有限公司						
NO.	PART NAME	MATERIAL	QTY	FINISHING	PRO.AGL:				REV :A4		