







3D VIEW





P.C.B LAYOUT  
TOP VIEW



- NOTES
1. CURRENT RATING: 1A.
  2. CONTACT RESISTANCE: 100mΩ MAX.
  3. INSULATION RESISTANCE: 100MΩ MIN.
  4. DIELECTRIC WITHSTANDING: 500V AC MIN.
  5. DURABILITY: 5000 CYCLES MIN.
  6. CONNECTOR MATING FORCES: 3~30N.
  7. CONNECTOR UNMATING FORCES: 3~30N.
  8. OPERATING TEMPERATURE: -25°C TO +85°C.



电话：0769-82320511-867

				TOLERANCE UNLESS SPECIFIED							
				UP TO 5mm: ±0.1	ANGULAR	1					
				ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD
7											
6	FAKE PIN	SUS	1								
5	HOUSING	PA9T	1	BLACK							
4	TERMINAL 4#	BRASS	1	Au-Plating	TITLE:PHONE JACK		UNIT : MM	ROHS	DWN		
3	TERMINAL 3#	SUS	1	Au-Plating	MODEL: PJ-3106LS-1		SCALE: 1:1	COMPLIANT	CHK'D		
2	TERMINAL 2#	PHORPHOS BRONZE	1	Au-Plating	 DONGGUANG HAOYU ELECTRONICS CO., LTD 皓宇 HOOYA 东莞市弘皓电子有限公司				APPD		
1	TERMINAL 1#	PHORPHOS BRONZE	1	Au-Plating							
NO.	PART NAME	MATERIAL	QTY	FINISHING					PRO.AGL:		REV :AO