




SPECIFICATIONS
 Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40°to+105°
 Contact Material: Brass
 Standard: PA6T
 Insulator Material: Polyester(UL 94V-0)
 Contact Plating: Gold Flash
 Max.Processing Temp: 240°C for30-60seconds
 (260°C for5seconds)



RECOMMEND P.C.B LAYOUT
 PCB TOLERANCE:±0.05 (TOP VIEW)

P/N	PIN	DIM.A	DIM.B
FH2.54-09-01PZD	1	0.00	2.54
FH2.54-09-02PZD	2	2.54	5.08
FH2.54-09-03PZD	3	5.08	7.62
FH2.54-09-04PZD	4	7.62	10.16
FH2.54-09-05PZD	5	10.16	12.70
FH2.54-09-06PZD	6	12.70	15.24
FH2.54-09-07PZD	7	15.24	17.78
FH2.54-09-08PZD	8	17.78	20.32
FH2.54-09-09PZD	9	20.32	22.86
.....
FH2.54-09-40PZD	40	(PIN-1)X2.54	(PIN)X2.54

PART NUMBER DESCRIPTION:

FH2.54-09-NPZD

↑ (D=单排;S=双排)
 ↑ (Z=直脚;W=弯脚)
 ↑ (PIN数量;01.....40PIN)
 ↑ (排针开关)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:2.54FH H8.5 1xnPin 180度 Y型 PC3.2 6T
DECIMALS:	ANGLES:		PAR FH2.54-09-NPZD
X.±0.30	X°±5'		DWN
X.X±0.20	X.X'±1'		CHKD
X.XX±0.10	X.XX'±0.5'	APVD	SCALE N:A UNIT:MM
CUSTOMER COPY		SIZE:A4	UNIT:MM
		SHEET:1F1	REV:A