

A B C D E F





REV	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
NEW	NEW DWG		2016-03-12

Current Rating: 3Amps  
 Insulator resistance: 5000 Megohms min.  
 Dielectric Withstanding: AC 500V  
 Operating Temperature: -40°C TO +105°C  
 Insulator Material: PA6T  
 Contact Material: Brass  
 Plating: Gold flash

UNSPECIFIED TOLERANCE: ±0.20

Dimensions List

Contacts	Dimensions		Contacts	Dimensions	
	A	B		A	B
2*1	2.54	0	2*21	53.34	50.80
2*2	5.08	2.54	2*22	55.88	53.34
2*3	7.62	5.08	2*23	58.42	55.88
2*4	10.16	7.62	2*24	60.96	58.42
2*5	12.70	10.16	2*25	63.50	60.96
2*6	15.24	12.70	2*26	66.04	63.50
2*7	17.78	15.24	2*27	68.58	66.04
2*8	20.32	17.78	2*28	71.12	68.58
2*9	22.86	20.32	2*29	73.66	71.12
2*10	25.40	22.86	2*30	76.20	73.66
2*11	27.94	25.40	2*31	78.74	76.20
2*12	30.48	27.94	2*32	81.28	78.74
2*13	33.02	30.48	2*33	83.82	81.28
2*14	35.56	33.02	2*34	86.36	83.82
2*15	38.10	35.56	2*35	88.90	86.36
2*16	40.64	38.10	2*36	91.44	88.90
2*17	43.18	40.64	2*37	93.98	91.44
2*18	45.72	43.18	2*38	96.52	93.98
2*19	48.26	45.72	2*39	99.06	96.52
2*20	50.80	48.26	2*40	101.6	99.06



PCB Layout

深圳市华德共创科技有限公司  
Shenzhen Huade co-create Technology Co., LTD  
电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表			TITLE: 产品名称: 2.54 双排针直插排针L11.6/3.0			
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDGCPH254-PZ02-X			
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001

A B C D E F