Part #: MALLORY Mallory Sonalert Products, Inc. ZT028LAIC2R Sales Outline Drawing Revision: F **INDIVIDUAL CONTROL OF LIGHT AND SOUND Specifications:** LIGHT SOUND Function Sound Level Category N/A Loud Continuous Fast Pulse @ 10 PPS Mode of Operation Lens Color **Opaque White** N/A LED Color **RED** N/A Rated Voltage 24 VAC/DC 24 VAC/DC Voltage Range 20 to 28 VAC/DC 20 to 28 VAC/DC Power Connection L~ to ~VAC/DC S~ to ~VAC/DC 25mA MAX **Current Draw** 25mA MAX

Housing Material 6/6 Nylon, Color: Black
Front Cap Material 6/6 Nylon, Color: Opaque White
Storage Temperature -40° to +80° C

Frequency
Loudness @ 2 FT

Storage Temperature -40° to +80° C
Operating Temperature -30° to +65° C

Panel Mounting Recommended hole size is 22.5 mm. Thread front will fit standard 22.5mm hole.

Knurled Nut Used to attach part to panel. The max recommended torque is 10 in-lbs.


Weight (Typical) 28 g

N/A

N/A

NEMA 3R,4X, & 12 Approved with use of included gasket.

Options Please contact factory.



3900 ± 500 Hz

85 to 95 dB(A) Typ.