Part #: MALLORY Mallory Sonalert Products, Inc. **ZA120MASU2 Sales Outline Drawing** Revision: F **Specifications:** Sound Level Category Medium Mode of Operation Fast Speed Up @ 0.5 -8 PPS in 30 Seconds Voltage Rating 48 to 120 VAC Frequency 3900 ± 500 Hz Loudness @ 2 FT 75 to 85 dB(A) Typ. **Current Draw** 40mA MAX Housing Material 6/6 Nylon, Color: Black Storage Temperature -40° to +80° C **Operating Temperature** -30° to +65° C **Panel Mounting** Recommended hole size is 22.5 mm. Thread front will fit standard 22.5mm hole. Knurled Nut Used to attach part to panel. The max recommended torque is 10 in-lbs. Weight (Typical) 28 g NEMA 3R,4X, & 12 Approved with use of included gasket. Supply voltage shall employ Transient Voltage Surge Suppression. Note Options Please contact factory. cUL Recognized **ROHS Compliant** Dimensions: Inches (mm) PATENT NUMBER 9576442 1.710 [43.44] 0.524 [13.31] 1.210 [30.74] Gasket

M22 x 1.5 Thread <0.86 Maj. Dia.

Knurl nut