





Specifications:






规格:

- Voltage rating: 50V AC/DC
- 额定电压: 50V AC/DC
- Current rating: 1A AC/DC
- 额定电流: 1A AC/DC
- Withstanding voltage: 500V AC/minute
- 耐受电压: 500V AC/分钟
- Temperature range: -25°C~+85°C
- 温度范围: -25°C~+85°C
- Insulation resistance: 100MΩ min
- 绝缘电阻: 100MΩ Min
- Contact resistance: 30mΩ Max
- 接触电阻: 30mΩ Max



X1010 W R S -XX -LP SN
 ① ② ③ ④ ⑤ ⑥ ⑦

1. Series No
2. Category: W-Wafer
3. Welding Board Angle: R-Stright 90°
4. Welding Way: S-SMT
5. Row No. Pin No: XX-02~15P
6. Material: LP-LCP UL94V-0
7. Plating: SN-Tin Plated
V01-Gold Flash



| Poles | Dimensions(mm) | | Poles | Dimensions(mm) | |
|-------|----------------|-------|-------|----------------|-------|
| | A | B | | A | B |
| 02 | 2.00 | 5.00 | 09 | 8.00 | 11.00 |
| 03 | 2.00 | 5.00 | 10 | 9.00 | 12.00 |
| 04 | 3.00 | 6.00 | 11 | 10.00 | 13.00 |
| 05 | 4.00 | 7.00 | 12 | 11.00 | 14.00 |
| 06 | 5.00 | 8.00 | 13 | 12.00 | 15.00 |
| 07 | 6.00 | 9.00 | 14 | 13.00 | 16.00 |
| 08 | 7.00 | 10.00 | 15 | 14.00 | 17.00 |

Recommended P.C.B Layout

| X1010WRS-XX-LPSN | LCP | Brass | X1010H |
|------------------|----------|---------------|----------------------|
| PART NO | Material | Material(Pin) | Suitable XKB Housing |

| | | | |
|------|--|-------------|--|
| DSND | | SCALE: N/A | MODEL TYPE: 1.0mm Crimp Style Connector |
| DWN | | VIEW: | PART NO.: X1010WRS-XX-LPSN |
| CHKD | | UNIT: mm/in | DWG NO.: X-X1010WRS-XX-LPSN |
| APPD | | SIZE: A4 | |



XKB INDUSTRIAL PRECISION CO., LIMITED

| WEIGHT | SHEET | REVISION |
|--------|-------|----------|
| | 1/1 | A0 |

| ANGLAR | ±5° |
|-------------|------|
| L ≤ 4 | ±0.2 |
| 4 < L ≤ 16 | ±0.3 |
| 16 < L ≤ 63 | ±0.4 |
| L > 63 | ±0.5 |

UNSPECIFIED TOLERANCES

| MARK | DESCRIPTION | DATE | REVISED | APPROVED |
|------|-------------|------|---------|----------|
| ΔX | | | | |
| ΔX | | | | |
| ΔX | | | | |

REVISIONS