


Patents, trademarks and copyrights and any articles or designs cited in this document are the property of their respective owners. Documents may contain information that is confidential or proprietary to a client of ODU-USA, Inc. and shall not be provided to a third party or duplicated in any form without written permission.

CAD: AutoCAD



Size	Part Number	Cable O.D. Range ( $\phi A$ )	
		Min.(In)	Max.(In)
1	701-023-XXX-965-025	2.5mm (0.09")	3.0mm (0.11")
1	701-023-XXX-965-030	3.0mm (0.11")	3.5mm (0.13")
1	701-023-XXX-965-035	3.5mm (0.13")	4.0mm (0.15")
1	701-023-XXX-965-040	4.0mm (0.15")	5.0mm (0.19")
1	701-023-XXX-965-050	5.0mm (0.19")	6.0mm (0.23")
1	701-023-XXX-965-060	6.0mm (0.23")	7.0mm (0.27")
1	701-023-XXX-965-070	7.0mm (0.27")	8.0mm (0.31")

Code	Color
202	Red
203	White
204	Yellow
205	Green
206	Blue
207	Gray
208	Black

Replace XXX with Color Code

Material: Silicone  
 Temperature: -50° to +200°  
 Short term to +230°  
 (Autoclavable)

ALL DIMENSIONAL UNITS ARE MILLIMETERS & INCHES UNLESS OTHERWISE STATED

Tolerance	Inches	Millimeters
.X	± 0.015	± .381
.XX	± 0.010	± .254
.XXX	± 0.005	± .127

COUNTRY CODE 301



otto dunkel gmbh

Project: Silicone Bend Relief, Size 1

DRAW:

CHECK:

APPROVED:

ODU P/N: 701-023-XXX-965-XXX

ODU DWG:

SHEET: 1/1

REV: 1

REVISION	INITIALS	REASON	DATE
1	RMo	INITIAL RELEASE	--