



技术说明

- 1.表明光洁, 无明显缩坑与熔接痕
2. Current rating: 14A AC/DC
额定电流: 14A AC/DC
3. 工作温度: -40°C - +125°C

K 282103 T F - P SN - X
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:T-Terminal
- 4.Special No:F-Female Terminal
- 5.Material:P-Phosphor Bronze
- 6.Plating:SN-Plated Tin
- 7.Type:H-High foot ; L-Middle foot
M-Low feet

K282103TF-PSN-M	AWG#22-20	2.5	2.3	0.6	4.8	4.7	1.8
K282103TF-PSN-L	AWG#18-15	3.05	3.3	1.2	4.6	4.8	1.8
K282103TF-PSN-H	AWG#15-13	3.6	3.8	1.2	4.8	4.7	1.8
PART NO	Wire Range	U	V	W	X	Y	Z

K282103TF-PSN-X	Phosphor Bronze	K282103HF	K282103D
PART NO	Material	Suitable XKB Female	Suitable XKB Plug

DSND	SCALE: N/A	MODEL TYPE: 6.0mm Automobile connector
DWN	VIEW:	PART NO.: K282103TF-PSN-X
CHKD	UNIT: mm/in	DWG NO.: X-K282103TF-PSN-X
APPD	SIZE: A4	WEIGHT SHEET REVISION 1/1 A0



XKB INDUSTRIAL PRECISION CO., LIMITED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

MARK	DESCRIPTION	DATE	REVISED	APPROVED
REVISIONS				
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn				