



Mating Height	PLUG	SOCKET
7.0	4.0	3.0
7.5	4.0	3.5
8.0	4.0	4.0
8.5	4.0	4.5

Specifications:
 规格:
 Voltage rating:50V AC/DC
 额定电压: 50V AC/DC
 Current rating:0.5A AC/DC
 额定电流: 0.5A AC/DC
 Withstanding voltage:200V AC/minute
 耐受电压: 200V AC/分钟
 Temperature range:-40°C--+85°C
 温度范围: -40°C--+85°C
 Insulation resistance: 100MΩ min
 绝缘电阻: 100MΩ Min
 Contact resistance:55mΩ Max
 接触电阻: 55mΩ Max

X0515 W V S-XX X S-9T V01
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- Series No
- Category:W-Wafer
- Welding Board Angle:V-Straight 180°
- Welding Way:S-SMT
- Row No.Pin No:XX-04-100P
- Height:A=4.0mm
- Special No:S-With positioning Columnm
- Material:9T-PA9T UL 94V-0 Black
- Plating:V01-Gold Flash

Poles	Dimensions					Poles	Dimensions				
	A	B	C	D	E		A	B	C	D	E
4	3.70	0.50	1.50	2.40		54	16.20	13.00	14.00	14.90	
6	4.20	1.00	2.00	2.90		56	16.70	13.50	14.50	15.40	
8	4.70	1.50	2.50	3.40		58	17.20	14.00	15.00	15.90	
10	5.20	2.00	3.00	3.90		60	17.70	14.50	15.50	16.40	
12	5.70	2.50	3.50	4.40		62	18.20	15.00	16.00	16.90	
14	6.20	3.00	4.00	4.90		64	18.70	15.50	16.50	17.40	
16	6.70	3.50	4.50	5.40		66	19.20	16.00	17.00	17.90	
18	7.20	4.00	5.00	5.90		68	19.70	16.50	17.50	18.40	
20	7.70	4.50	5.50	6.40		70	20.20	17.00	18.00	18.90	
22	8.20	5.00	6.00	6.90		72	20.70	17.50	18.50	19.40	
24	8.70	5.50	6.50	7.40		74	21.20	18.00	19.00	19.90	
26	9.20	6.00	7.00	7.90		76	21.70	18.50	19.50	20.40	
28	9.70	6.50	7.50	8.40		78	22.20	19.00	20.00	20.90	
30	10.20	7.00	8.00	8.90		80	22.70	19.50	20.50	21.40	
32	10.70	7.50	8.50	9.40		82	23.20	20.00	21.00	21.90	
34	11.20	8.00	9.00	9.90		84	23.70	20.50	21.50	22.40	
36	11.70	8.50	9.50	10.40		86	24.20	21.00	22.00	22.90	
38	12.20	9.00	10.00	10.90		88	24.70	21.50	22.50	23.40	
40	12.70	9.50	10.50	11.40		90	25.20	22.00	23.00	23.90	
42	13.20	10.00	11.00	11.90		92	25.70	22.50	23.50	24.40	
44	13.70	10.50	11.50	12.40		94	26.20	23.00	24.00	24.90	
46	14.20	11.00	12.00	12.90		96	26.70	23.50	24.50	25.40	
48	14.70	11.50	12.50	13.40		98	27.20	24.00	25.00	25.90	
50	15.20	12.00	13.00	13.90		100	27.70	24.50	25.50	26.40	
52	15.70	12.50	13.50	14.40							

PART NO	Material	Material(Pin)	Suitable XKB Female
X0515WS-XXXS-9TV01	PA9T	Phosphor Bronze	X0515F

DSND	SCALE: N/A	MODEL TYPE:		
DWN	VIEW:	0.5mm BTB Style Connector		
CHKD	UNIT: mm/in	PART NO.: X0515WS-XXXS-9TV01		
APPD	SIZE: A4	DWG NO.: X-X0515WS-XXXS-9TV01		
		WEIGHT	SHEET	REVISION
			1/1	A0



XKB INDUSTRIAL PRECISION CO.,LIMITED

广东星坤科技股份有限公司

DATE	DESCRIPTION	REVISIONS

文件工程章

DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES