



Electrical specifications

Center Frequency: 770 MHz
Bandwidth: 37.5 MHz min.
VSWR: 1.5 : 1
Input / Output Impedance: 50 Ohms
Passband: 751.25-788.75 MHz
Passband Insertion Loss: 1.0 dB max
Passband Ripple: 1.0 dB max
Rejection: 40 dB min
Rejection 2: 1000 MHz
Power Handling: 5 W

Mechanical

Mounting Method: SMT
Dimensions: 17 x 13 x 5.5 mm

Environmental

Operating Temperature: -20°C to +70°C
Storage Temperature: -50°C to +90°C

This product is RoHs compliant.

Outline Drawing:

