



ANATECH ELECTRONICS INC
RF & Microwave Filters & Products

895 MHz Ceramic Bandpass Filter

Part Number: **AM895B1367**



Electrical specifications

Center Frequency: 895 MHz
Bandwidth: 40 MHz
VSWR in BW: 1.5 : 1
Input / Output Impedance: 50 Ohms
Passband: 875-915 MHz
Passband Insertion Loss: 3.0 dB max.
Passband Ripple: 1.0 dB max.
Rejection: 25 dB min at 855 MHz
Rejection 2: 22 dB min at 935 MHz
Power Handling: 2 W

Mechanical

Mounting Method: SMT
Dimensions: 38mm x 17mm x 7.5mm

Environmental

Operating Temperature: -10°C to 50°C
Storage Temperature: -50°C to +90°C

This product is RoHs compliant.

Outline Drawing:

