



**Electrical specifications**

**Center Frequency:** 782 MHz  
**Bandwidth:** 5 MHz min.  
**VSWR:** 1.7 : 1  
**Input / Output Impedance:** 50 Ohms  
**Passband:** 779.5-784.5 MHz  
**Passband Insertion Loss:** 4.0 dB max  
**Passband Ripple:**  
**Rejection:** 25 dB min at 746–756 MHz  
**Rejection 2:** 30 dB min at 930.6–940.3 MHz  
**Rejection 3:** 50 dB min at 1084.2–1094.2 MHz  
**Power Handling:** 2 W

**Mechanical**

**Mounting Method:** SMT  
**Dimensions:** 17 x 13 x 5.5 mm

**Environmental**

**Operating Temperature:** -20°C to +70°C  
**Storage Temperature:** -50°C to +90°C

**This product is RoHs compliant.**

**Outline Drawing:**

